

MediaWorkStation Technic

Comparison chart

Feature / Edition	Select	Basic technic 2.9
	2.7	
Compatibility		
Microsoft Windows (latest information on www.mediaworkstation.de/maintenance.html)	7 / Vista / XP	10 / 8 / 7 / Vista
Maximum display resolution for exclusive program presentation	1680 x 1050	2048 x 1536
SD Video (PAL / NTSC)	\checkmark	\checkmark
HD Video (720p / 1024p / 1080i / 1080p)		\checkmark
Languages	EN/DE/FR/ES IT/ RU	EN / DE
Operation		
Constant user front end during the entire operation	✓	✓
Demo period of 30 days / then activation via activation key is necessary	✓	✓
Record control by foot switch, USB or camera	✓	✓
During recording live image and single pictures shown in tiles	\checkmark	\checkmark
Optimized for touch operation	✓	✓
Comment & Report		
Pictures extraction from video	✓	\checkmark
Storage of extracted pictures from video into database		\checkmark
Entering of session comments		\checkmark
Entering of dataset comments	✓	✓
Entering of graphics markers with text into pictures		✓
Predefined texts for comments		✓
Interactive comment editor		\checkmark
Creation of configurable HTML reports with images		\checkmark
Image optimization VICA®		
Real time image processing for suppressing brightness variations under flashlight (SD Video)	\checkmark	\checkmark
Automatic removal of black margins at image print-outs	\checkmark	✓



MediaWorkStation Technic

Comparison chart

Feature / Edition	Select	Basic technic 2.9
	2.7	
Export & Print		
Export of pictures with embedded patient data and additional information	\checkmark	\checkmark
Direct print-out of pictures to individual printer	\checkmark	\checkmark
Direct print-out of pictures with embedded patient data and additional information		\checkmark
Database		
Recording of pictures and videos	✓	\checkmark
Sessions summarizes recordings by date	✓	\checkmark
Projects summarizes sessions		\checkmark
Full text search for comments	✓	\checkmark
Application specific comment database		\checkmark
Project management separated by application		\checkmark
Search and sort by project data		\checkmark
Ring storage (FiFo) for recordings with automatic capacity control		\checkmark
Centralized database with mutual exclusive access by one client		\checkmark
Security		
Encrypted file names of recordings	√	\checkmark
Automatic database backup providing selectable interval	√	\checkmark
Automatic archiving of recordings onto external data carrier		\checkmark
Automatic system check and repair during programme start-up		\checkmark
System configuration secured by password		✓
Configuration		
Wizard for video device configuration	\checkmark	\checkmark
Changeover between device configurations	✓	\checkmark